



Eaton CM32FG

Fuse accessory, Fuse-holder, low voltage, 32 A, AC 690 V, BS88/A2, 1P, BS, DIN rail or screw mounting, green, fuse-link AAO

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse holder
CATALOG NUMBER	CM32FG
PRODUCT LENGTH/DEPTH	31.8 mm
PRODUCT HEIGHT	93.7 mm
PRODUCT WIDTH	60 mm
PRODUCT WEIGHT	162.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269



Powering Business Worldwide

□□□□	
AMPERAGE RATING	32 A
CONNECTION TYPE	Screwed terminal
FEATURES	Halogen free
NUMBER OF POLES	Single-pole
VOLTAGE RATING AT AC	690 V a.c.
FUSE TYPE	TIA AAO
ACCESSORIES	32BS, 32CML, 32LSC, NI
COLOR	Green
BUS-MOUNTING TYPE	Yes
CONNECTION	Front Connected
CONSTRUCTION SIZE	Other
MOUNTING METHOD	DIN rail
TYPE	fuse accessory
APPLICATION	general industrial applications
MODEL	Camaster

□□	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-british-standard-fuse-holder-declaration-of-conformity-uk251074en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

