



Eaton CPMV3L-UNV1

Eaton Crouse-Hinds series Champ CPMV LED wall pack, 0.09A, Cool white, Dimmable driver, 3/4" entry, 70W equiv, 50/60 Hz, Tempered glass lens, 3000 lumens, 111 lm/W, Die cast alum, Yoke mount, 7x6 distribution, 120-277 Vac, 125-250 Vdc, 30W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ CPMV LED wall pack light fixture
CATALOG NUMBER	CPMV3L-UNV1
UPC	662276936232
PRODUCT LENGTH/DEPTH	9.16 in
PRODUCT HEIGHT	12.76 in
PRODUCT WIDTH	12.6 in
PRODUCT WEIGHT	14 lb



Powering Business Worldwide


Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	LED
LUMENS	3000
LUMENS PER WATT	111
COLOR TEMPERATURE	Cool white
OPTICAL DISTRIBUTION	7x6
MOUNTING METHOD	Yoke
VOLTAGE RATING	120-277 Vac, 125-250 Vdc
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Tempered glass
WATTAGE	30W
AMPERAGE RATING	0.09 A
POWER FACTOR	> 0.90
DIMMING	Dimmable driver
ENTRY SIZE	3/4"
MATERIAL	Die cast aluminum
EQUIVALENT LUMINAIRE	70W

Links

3D 	SP3D Design Package - Champ CPMV LED Hazardous Area Wallpack Light Fixtures
	IF 1892 - Champ-Pak CPMVL LED Wall Pack
	Eaton Specification Sheet - CPMV3L-UNV1
	Crouse-Hinds series CPMV LED brochure Crouse-Hinds series Global LED lighting portfolio
	Crouse-Hinds series Champ CPMV LED catalog page
	Champ CPMV LED Hazardous Area Wallpack Light Fixtures UL certification Champ CPMV LED Hazardous Area Wallpack Light Fixtures Canadian certification

