



□□□□□

Eaton CPMV5L-UNV1-S891

Eaton Crouse-Hinds series Champ CPMV LED wall pack, 0.15A, Cool white, Dimmable driver, 3/4" entry, 100W equiv, 50/60 Hz, Diffused glass lens, 5000 lumens, 116 lm/W, Die cast alum, Yoke mount, 7x6 distribution, 120-277 Vac, 125-250 Vdc, 45W


□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ CPMV LED wall pack light fixture
CATALOG NUMBER	CPMV5L-UNV1-S891
UPC	662276892033
PRODUCT LENGTH/DEPTH	9.16 in
PRODUCT HEIGHT	12.76 in
PRODUCT WIDTH	12.6 in
PRODUCT WEIGHT	14 lb

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class III Class II, Division 1
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications	
LAMP TYPE	LED
LUMENS	5000
LUMENS PER WATT	26W
COLOR TEMPERATURE	Cool white
OPTICAL DISTRIBUTION	7x6
MOUNTING METHOD	Yoke
VOLTAGE RATING	120-277 Vac, 125-250 Vdc
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Diffused glass
WATTAGE	45W
AMPERAGE RATING	0.088A
POWER FACTOR	> 0.90
DIMMING	Dimmable driver
ENTRY SIZE	3/4"
MATERIAL	Die cast aluminum
EQUIVALENT LUMINAIRE	100W

Links

3D 	SP3D Design Package - Champ CPMV LED Hazardous Area Wallpack Light Fixtures
	IF 1892 - Champ-Pak CPMVL LED Wall Pack
	Eaton Specification Sheet - CPMV5L-UNV1-S891
	Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series CPMV LED brochure
	Crouse-Hinds series Champ CPMV LED catalog page
	Champ CPMV LED Hazardous Area Wallpack Light Fixtures Canadian certification Champ CPMV LED Hazardous Area Wallpack Light Fixtures UL certification

