



□□□□□

## Eaton CPMV7L-UNV34-S891

Eaton Crouse-Hinds series Champ CPMV LED wall pack, 0.21A, Cool white, Dimmable driver, 3/4" entry, 150-175W equiv, 60 Hz, Diffused glass lens, 7000 lumens, 115 lm/W, Die cast aluminum, Yoke mount, 7x6 distribution, 347-480 Vac, 59W

□□□□

|                             |                                                                  |
|-----------------------------|------------------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Crouse-Hinds series Champ CPMV LED wall pack light fixture |
| <b>CATALOG NUMBER</b>       | CPMV7L-UNV34-S891                                                |
| <b>UPC</b>                  | 662276892156                                                     |
| <b>PRODUCT LENGTH/DEPTH</b> | 9.16 in                                                          |
| <b>PRODUCT HEIGHT</b>       | 12.76 in                                                         |
| <b>PRODUCT WIDTH</b>        | 12.6 in                                                          |
| <b>PRODUCT WEIGHT</b>       | 14 lb                                                            |

| Certifications and compliances  |                                                          |
|---------------------------------|----------------------------------------------------------|
| AREA CLASSIFICATION             | Hazardous/Classified Locations                           |
| STANDARDS TYPE                  | NEC/CEC                                                  |
| NEC HAZARDOUS RATING            | Class III<br>Class I, Division 2<br>Class II, Division 1 |
| NEMA RATING                     | 4X                                                       |
| INGRESS PROTECTION (IP) RATINGS | IP66                                                     |

| Product specifications |                   |
|------------------------|-------------------|
| LAMP TYPE              | LED               |
| LUMENS                 | 7000              |
| LUMENS PER WATT        | 115               |
| COLOR TEMPERATURE      | Cool white        |
| OPTICAL DISTRIBUTION   | 7x6               |
| MOUNTING METHOD        | Yoke              |
| VOLTAGE RATING         | 347-480 Vac       |
| FREQUENCY RATING       | 60 Hz             |
| LENS MATERIAL          | Diffused glass    |
| WATTAGE                | 59 W              |
| AMPERAGE RATING        | 0.21 A            |
| POWER FACTOR           | > 0.90            |
| DIMMING                | Dimmable driver   |
| ENTRY SIZE             | 3/4"              |
| MATERIAL               | Die cast aluminum |
| EQUIVALENT LUMINAIRE   | 150-175W          |

## 

|    |                                                                                                                                                                                            |
|----|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 3D | <a href="#">SP3D Design Package - Champ CPMV LED Hazardous Area Wallpack Light Fixtures</a>                                                                                                |
|    | <a href="#">IF 1892 - Champ-Pak CPMVL LED Wall Pack</a>                                                                                                                                    |
|    | <a href="#">Eaton Specification Sheet - CPMV7L-UNV34-S891</a>                                                                                                                              |
|    | <a href="#">Crouse-Hinds series Global LED lighting portfolio</a><br><br><a href="#">Crouse-Hinds series CPMV LED brochure</a>                                                             |
|    | <a href="#">Crouse-Hinds series Champ CPMV LED catalog page</a>                                                                                                                            |
|    | <a href="#">Champ CPMV LED Hazardous Area Wallpack Light Fixtures UL certification</a><br><br><a href="#">Champ CPMV LED Hazardous Area Wallpack Light Fixtures Canadian certification</a> |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,     
Eaton.com

© 2025   

Follow us on social media to get the latest product and support information.

