

Eaton CPP516

Eaton Crouse-Hinds series Arktite CPP plug, 20A, 0.312-0.625" cable diameter, Two-wire, three-pole, Brass contacts, 60 Hz, Style 2, 1 HP, Copper-free aluminum, Factory sealed, Delayed action circuit breaking, 125-250 Vac/18 Vdc

PRODUCT NAME	Eaton Crouse-Hinds series Arktite CPP plug
CATALOG NUMBER	CPP516
UPC	782274175102
PRODUCT LENGTH/DEPTH	8.38 in
PRODUCT HEIGHT	1.75 in
PRODUCT WIDTH	1.75 in
PRODUCT WEIGHT	0.8 lb

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2
SPECIAL FEATURES	Factory sealed
TYPE	Delayed action circuit breaking
AMPERAGE RATING	20A
VOLTAGE RATING	125-250 Vac/18 Vdc
CONTACT MATERIAL	Brass
CONFIGURATION	Two-wire, three-pole
FREQUENCY RATING	60 Hz
GROUNDING STYLE	Style 2
HORSEPOWER	1 hp
MATERIAL	Copper-free aluminum
CABLE DIAMETER	0.312-0.625 in

IF 285 - CPP Plugs	
Eaton Specification Sheet - CPP516	
Arktite CPS and CPP Explosionproof Receptacles and Plugs catalog page	
Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors Canadian certification	
Arktite CPS, CPP, CPR Explosionproof Receptacles, Plugs and Connectors UL certification	

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com
 © 2025

Follow us on social media to get the latest product and support information.