

Eaton CRIG-15S4-20M

Eaton Crouse-Hinds series Roughneck CRIG cable mounted receptacle with mechanical clamp, 796A, 1.125-1.250", Female, Silver plated copper contacts, 444 kcmil, Socket, Glove nut, C24 shell

PRODUCT NAME	Eaton Crouse-Hinds series Roughneck CRIG cable mounted receptacle with mechanical clamp
CATALOG NUMBER	CRIG-15S4-20M
UPC	662276656734
PRODUCT LENGTH/DEPTH	8.69 in
PRODUCT HEIGHT	3.56 in
PRODUCT WIDTH	3.56 in
PRODUCT WEIGHT	3.5 lb

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	6P 4X
INGRESS PROTECTION (IP) RATINGS	IP68
AMPERAGE RATING	796 A
CONTACT MATERIAL	Silver plated copper
CONTACT TYPE	Socket
CABLE HARDWARE	Mechanical Clamp
CONNECTOR GENDER	Female
CONTACT SIZE	444 kcmil
COUPLING NUT	Glove nut
SHELL SIZE	C24
CABLE DIAMETER RANGE	1.125-1.250 in

	IF 1688 - Roughneck Non-hazardous Multi-pin Connector
	Multi-pin Connectors
	Eaton Specification Sheet - CRIG-15S4-20M
	Roughneck Multi-pin and Single Pole Connectors brochure
	Roughneck Heavy Industrial Multi-pin and Single Pole Connectors catalog page
	Roughneck Heavy Industrial Multi-pin Connectors UL certification (CRIG Series)
	Roughneck Heavy Industrial Multi-pin Connectors Canadian certification (CRIG Series)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

