



□□□□□

Eaton CSM01751

CSM01751,MATSN-125/63/2H□-EN

□□□□

PRODUCT NAME	Eaton MATSN automatic transfer switch
CATALOG NUMBER	CSM01751
PRODUCT LENGTH/DEPTH	163 mm
PRODUCT HEIGHT	250 mm
PRODUCT WIDTH	258 mm
PRODUCT WEIGHT	6.5 kg
CERTIFICATIONS	CE CCC CB

□□□□

□□

NOMINAL INPUT VOLTAGE	220 V
-----------------------	-------

FREQUENCY RATING	50/60 Hz
------------------	----------

INPUT VOLTAGE - MIN	220 V
---------------------	-------

INPUT VOLTAGE - MAX	220 V
---------------------	-------

NOMINAL INPUT CURRENT SHORE	63 A
-----------------------------	------

TRANSFER TIME SWITCH ON - MIN	0 ms
-------------------------------	------

TRANSFER TIME SWITCH ON - MAX	100 ms
-------------------------------	--------

TRANSFER TIME SWITCH OFF - MIN	0 ms
--------------------------------	------

TRANSFER TIME SWITCH OFF - MAX	100 ms
--------------------------------	--------

AMBIENT TEMPERATURE - MIN	-20 °C
---------------------------	--------

AMBIENT TEMPERATURE - MAX	55 °C
---------------------------	-------

NUMBER OF POLES	Two-pole
-----------------	----------

CONTROLLER TYPE	Type H Separate controller
-----------------	----------------------------

NUMBER OF POSITIONS	2
---------------------	---

RATED CURRENT	63 A
---------------	------

RATED INSULATION VOLTAGE	800 V
--------------------------	-------

RATED IMPULSE WITHSTAND VOLTAGE UIMP	8 kV
--------------------------------------	------

RATED OPERATIONAL VOLTAGE UE AT 50/60HZ	220 V
---	-------

POLLUTION DEGREE	3
------------------	---

WIRING METHOD	Front panel wiring
---------------	--------------------

FRAME SIZE	1
------------	---

RATED SHORT TIME MAKING CAPACITY ICM	7.65 kA
--------------------------------------	---------

UTILIZATION CATEGORY	AC-33iB AC-33B AC-33iA
----------------------	------------------------------

