



□□□□□

Eaton CSM01771

CSM01771,MATSN-125/32/4H□-EN

□□□□

PRODUCT NAME	Eaton MATSN automatic transfer switch
CATALOG NUMBER	CSM01771
PRODUCT LENGTH/DEPTH	163 mm
PRODUCT HEIGHT	250 mm
PRODUCT WIDTH	319 mm
PRODUCT WEIGHT	8.5 kg
CERTIFICATIONS	CE CCC CB

□□□□

□□

NOMINAL INPUT VOLTAGE	400 V
FREQUENCY RATING	50/60 Hz
INPUT VOLTAGE - MIN	400 V
INPUT VOLTAGE - MAX	400 V
NOMINAL INPUT CURRENT SHORE	32 A
TRANSFER TIME SWITCH ON - MIN	0 ms
TRANSFER TIME SWITCH ON - MAX	100 ms
TRANSFER TIME SWITCH OFF - MIN	0 ms
TRANSFER TIME SWITCH OFF - MAX	100 ms
AMBIENT TEMPERATURE - MIN	-20 °C
AMBIENT TEMPERATURE - MAX	55 °C
NUMBER OF POLES	Four-pole
CONTROLLER TYPE	Type H Separate controller
NUMBER OF POSITIONS	2
RATED CURRENT	32 A
RATED INSULATION VOLTAGE	800 V
RATED IMPULSE WITHSTAND VOLTAGE UIMP	8 kV
RATED OPERATIONAL VOLTAGE UE AT 50/60HZ	400 V
POLLUTION DEGREE	3
WIRING METHOD	Front panel wiring
FRAME SIZE	1
RATED SHORT TIME MAKING CAPACITY ICM	7.65 kA
UTILIZATION CATEGORY	AC-33iB AC-33B AC-33iA

