



□□□□

Eaton D3899920ZF18SN

Aluminium square flange receptacle, Black Zinc Nickel plating, with female contacts; D3899920ZF18SN

□□□□

PRODUCT NAME	Eaton Souriau D38999 SIII / 8D series milaero connectors
CATALOG NUMBER	D3899920ZF18SN
PRODUCT LENGTH/DEPTH	34.1 mm
PRODUCT HEIGHT	36.5 mm
PRODUCT WIDTH	36.5 mm
PRODUCT WEIGHT	29 g



Powering Business Worldwide

□□□□

FITTED WITH:	Shielding
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Crimp
COUPLING TYPE	Thread
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Peek
LAYOUT	18
PLATING	Black Zinc Nickel
SHELL CONTINUITY	2.5
SHELL MATERIAL	Aluminium
SHELL SIZE	19
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	200 °C
OPERATING TEMPERATURE - MIN	-65 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #22D	14
NUMBER OF CAVITY #8 POWER	4
SALT SPRAY	500 hour
WORKING VOLTAGE (VRMS)	1300 V

□□

