



Eaton DD200M315

Eaton Bussmann series low voltage British standard fuse, Fuse-link, LV, 200 A, AC 415 V, BS88/B2, 31 x 136 mm, gM, BS, 200M315

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	DD200M315
UPC	051712839617
PRODUCT LENGTH/DEPTH	136 mm
PRODUCT HEIGHT	31 mm
PRODUCT WIDTH	31 mm
PRODUCT WEIGHT	153.2 g
COMPLIANCES	RoHS Compliant



Powering Business Worldwide

AMPERAGE RATING	315 A
FITTED WITH:	Centre bolted tags
FUSE SIZE	BS88/B2
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
MOTOR CURRENT RATING	200M315
RATED VOLTAGE AC	415 V
CLASS	Class gM
FUSE TYPE	DD
UTILIZATION CATEGORY	gM (motor protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	9 W
CONNECTION	111 mm fixing centre
CONSTRUCTION	BS88/B2
CONSTRUCTION SIZE	B2
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC
SUITABLE FOR	RS200 Red spot fuse holder
MOUNTING METHOD	200DF fuseblock
QUANTITY	5
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

