

Eaton DD322FDKW-00V2

Eaton Double door single-throw fused safety switch, Voltage indicator load side, 60 A, NEMA 12/3R, Fusible without neutral, Three-pole, Three-wire, 240 V, Max Hp: 20, 25/ 30, 50 hp (1/3PH @480, 600 V), #14-#2

PRODUCT NAME	Eaton double door single-throw fused safety switch
CATALOG NUMBER	DD322FDKW-00V2
UPC	786679177457
PRODUCT LENGTH/DEPTH	37.49 in
PRODUCT HEIGHT	8.22 in
PRODUCT WIDTH	12.33 in
PRODUCT WEIGHT	37 lb
CERTIFICATIONS	UL Listed
CATALOG NOTES	Double Door Isolation Switch w/ Load Side Voltage Indicator

SPECIAL FEATURES	V indicator load side, w/ window
TYPE	Heavy duty double door safety switch
AMPERAGE RATING	60A
NUMBER OF POLES	Three-pole
PRODUCT CATEGORY	Dust tight
VOLTAGE RATING	240V
HP RATING - MAX	20, 25/ 30, 50 hp (1/3PH @480, 600 V)
WIRE SIZE	#14-2 AWG
ENCLOSURE	NEMA 12, NEMA 3R
ENCLOSURE MATERIAL	Painted galvanized steel
FUSE CLASS PROVISION	Class H
FUSE CONFIGURATION	Fusible without neutral
NUMBER OF WIRES	3
NEMA RATING	NEMA 12

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

