

## Eaton DEO125

Eaton Bussmann series low voltage british standard fuse, 125A, AC 415 V, 31 x 110 mm, gL/gG

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	DEO125
<b>UPC</b>	051712839624
<b>PRODUCT LENGTH/DEPTH</b>	110 mm
<b>PRODUCT HEIGHT</b>	29.5 mm
<b>PRODUCT WIDTH</b>	31 mm
<b>PRODUCT WEIGHT</b>	144.4 g
<b>COMPLIANCES</b>	RoHS Compliant

AMPERAGE RATING	125 A
FITTED WITH:	Offset bolted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	93.7 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	DEO
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	11 W
CONNECTION	94 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

