



□□□□

## Eaton DET-RDT-G2

Motion (Dual Tech), Radio, Plastic, White

□□□□

<b>PRODUCT NAME</b>	Eaton motion sensor
<b>CATALOG NUMBER</b>	DET-RDT-G2
<b>PRODUCT LENGTH/DEPTH</b>	55 mm
<b>PRODUCT HEIGHT</b>	114 mm
<b>PRODUCT WIDTH</b>	55 mm
<b>PRODUCT WEIGHT</b>	0.17 kg
<b>CERTIFICATIONS</b>	CE marking



Powering Business Worldwide

□□□□

<b>CHANNELS</b>	1
<b>CHARACTERISTIC</b>	Other
<b>COMPLIANCE</b>	Certified to EN50131-2-4
<b>CONNECTION</b>	Radio
<b>COVER MONITORING</b>	Yes
<b>CURRENT NORMAL</b>	0.02 mA
<b>DETECTION ANGLE - MIN</b>	90 °
<b>DETECTION RANGE - MAX</b>	12 m
<b>DETECTION RANGE</b>	90 °
<b>FREE SPACE RADIO RANGE</b>	800 m
<b>OPERATING HUMIDITY - MAX</b>	93 %
<b>OPERATING CURRENT</b>	0.02 mA
<b>OPERATING TEMPERATURE - MAX</b>	55 °C
<b>OPERATING TEMPERATURE - MIN</b>	-10 °C
<b>OPERATING VOLTAGE - MAX</b>	4.5 V
<b>OPERATING VOLTAGE - MIN</b>	3.4 V
<b>PET TOLERANT</b>	No
<b>POWER SUPPLY</b>	3.4 V
<b>TYPE OF DETECTOR</b>	Motion (Dual Tech)
<b>RADIO SYSTEM</b>	Yes
<b>REPLACEMENT BATTERY CODE</b>	1-345346 / 3v CR2
<b>TAMPER PROTECTION</b>	Yes
<b>TRANSMISSION POWER</b>	10 mW
<b>TYPE OF MESSAGING</b>	Active infrared (beam)
<b>TYPICAL BATTERY LIFE</b>	24 monthly
<b>VDS</b>	None
<b>BATTERY TYPE</b>	Not applicable
<b>BATTERY QUANTITY</b>	3
<b>MOUNTING METHOD</b>	Surface Surface mounting

□□

