



□□□□□

Eaton DU1001-0000

Eaton DU Duplex Low Pressure Filter,
DU1001.10VG.10.B.P.-.FS.A.P.-.-, 10 VG,
Glass fiber fleece (VG), Nitrile, 464 psi (32
Bar), Non-bypass

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU1001-0000
PRODUCT LENGTH/DEPTH	587.27 mm
PRODUCT HEIGHT	721.01 mm
PRODUCT WIDTH	243.01 mm
PRODUCT WEIGHT	120.19 kg
	ATEX Directive 2014/34/EU
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. AD 2000



Powering Business Worldwide

0000

CONNECTION TYPE	3" SAE/ANSI flange
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
RETENTION RATING	7.0 µ m
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	None
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	80 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

