



□□□□□

Eaton DU1001-0001

Eaton DU Duplex Low Pressure Filter,
DU1001.10VG.10.B.P.-.FS.A.P.-.S.AE.50.1,5.P.-
.B, 10 VG, Glass fiber fleece (VG), Nitrile, 464
psi (32 Bar), Bypass set at 29 psi (2 Bar)

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU1001-0001
PRODUCT LENGTH/DEPTH	587.27 mm
PRODUCT HEIGHT	721.01 mm
PRODUCT WIDTH	291.77 mm
PRODUCT WEIGHT	120.19 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000



Powering Business Worldwide

0000		00	
CONNECTION TYPE	3" SAE/ANSI flange		
FILTER TYPE	Duplex filter		
MATERIAL	EN-GJS-400-18-LT		
APPLICATION	For continuous operation. Mount in suction, pressure or return lines		
SPECIFICATION	Standard		
CODE STAMP	None		
FILTER FINENESS	10 VG		
FILTER MEDIA TYPE	Glass fiber fleece (VG)		
FLUID GROUP (DGRL 2014/68/EU)	2		
INDICATOR TYPE	Electrical/Visual		
SEALING MATERIAL	Nitrile		
ELEMENT COLLAPSE RATING	145 psi (10 Bar)		
OPERATING TEMPERATURE - MAX	100 °C		
OPERATING TEMPERATURE - MIN	-10 °C		
VALVE CONFIGURATION OPTIONS	Bypass set at 29 psi (2 Bar)		
OPERATING PRESSURE - MAX	464 psi (32 Bar)		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: