



□□□□□

Eaton DU1001-0005

Eaton DU Duplex Low Pressure Filter,
DU.1001.10VG.10.B.P.-.FS.A.-.S.AE.30.1,5.P.-
.B, 10VG, Glass fiber fleece (VG), Nitrile, 464
psi (32 Bar), Bypass set at 29 psi (2 Bar)

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU1001-0005
PRODUCT LENGTH/DEPTH	584.97 mm
PRODUCT HEIGHT	721.01 mm
PRODUCT WIDTH	291.77 mm
PRODUCT WEIGHT	120.21 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000 2006/95/EC



Powering Business Worldwide

0000

CONNECTION TYPE	3" SAE/ANSI flange
DESIGN	Double open end
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 29 psi (2 Bar)
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

