



□□□□□

Eaton DU1001-0011

Eaton DU Duplex Low Pressure Filter, DU 1001.25API.10.B.P.-.FS.A.IS20.S1.-, 25API, Glass fiber fleece (API), Nitrile, 232 psi (16 Bar), Bypass set at 51 psi (3.5 Bar)

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU1001-0011
PRODUCT LENGTH/DEPTH	584.97 mm
PRODUCT HEIGHT	721.01 mm
PRODUCT WIDTH	243.01 mm
PRODUCT WEIGHT	120.21 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000 2006/95/EC

0000

CONNECTION TYPE	3" SAE/ANSI flange
DESIGN	Double open end
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	IS20
FILTER FINENESS	25 API
FILTER MEDIA TYPE	Glass fiber fleece (API)
INDICATOR TYPE	None
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 51 psi (3.5 Bar)
OPERATING PRESSURE - MAX	232 psi (16 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

