



□□□□□

Eaton DU1001-0373

Eaton DU Duplex Low Pressure Filter,
DU1001.25API.10.B.P.-.FS.A.-.-.OE1.0,8.B.-
.P., 25 API, Glass fiber fleece (API), Nitrile,
464 psi (32 Bar), Non-bypass

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU1001-0373
PRODUCT LENGTH/DEPTH	587.27 mm
PRODUCT HEIGHT	721.01 mm
PRODUCT WIDTH	353.01 mm
PRODUCT WEIGHT	120.19 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000

0000	
CONNECTION TYPE	3" SAE/ANSI flange
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	25 API
FILTER MEDIA TYPE	Glass fiber fleece (API)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

