



□□□□□

Eaton DU101-0002

Eaton DU Duplex Low Pressure Filter,
DU.101.10VG.16.S.P.-.FS.6.-.AE.50.2,5.P.-.B,
10VG, Glass fiber fleece (VG), Nitrile, 464 psi
(32 Bar), Bypass set at 29 psi (2 Bar)

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU101-0002
PRODUCT LENGTH/DEPTH	294.01 mm
PRODUCT HEIGHT	463 mm
PRODUCT WIDTH	198.79 mm
PRODUCT WEIGHT	23.14 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000 2006/95/EC

0000	
CONNECTION TYPE	1 1/4" SAE/ANSI flange
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	232 psi (16 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 29 psi (2 Bar)
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

