



□□□□□

Eaton DU101-0010

Eaton DU Duplex Low Pressure Filter,
DU.101.10VG.16.S.P.-.FS.6.P.-.AOR.1,5.P.-,
10VG, Glass fiber fleece (VG), Nitrile, 464 psi
(32 Bar), Bypass set at 29 psi (2 Bar)

□□□□

PRODUCT NAME	Eaton DU Duplex Low Pressure Filter
CATALOG NUMBER	DU101-0010
PRODUCT LENGTH/DEPTH	294.01 mm
PRODUCT HEIGHT	463 mm
PRODUCT WIDTH	198.79 mm
PRODUCT WEIGHT	23.14 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000 2006/95/EC



Powering Business Worldwide

0000	
CONNECTION TYPE	1 1/4" SAE/ANSI flange
FILTER TYPE	Duplex filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	For continuous operation. Mount in suction, pressure or return lines
SPECIFICATION	Standard
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
INDICATOR TYPE	Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	232 psi (16 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 29 psi (2 Bar)
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000 Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

