

Eaton E1017-1608

Eaton Crouse-Hinds series Cam-Lok J Series E1017 threaded stud receptacle, Up to 690A continuous, 350-750 kcmil, Green, Male, Rubber, 1/2"-13, 90° angle, 600 Vac/dc

PRODUCT NAME	Eaton Crouse-Hinds series Cam-Lok J Series E1017 threaded stud receptacle
CATALOG NUMBER	E1017-1608
UPC	662275132673
PRODUCT LENGTH/DEPTH	5.88 in
PRODUCT HEIGHT	4.5 in
PRODUCT WIDTH	4.5 in
PRODUCT WEIGHT	3.34 lb

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3R
AMPERAGE RATING	Up to 690A Continuous
VOLTAGE RATING	600 Vac/dc
CABLE SIZE	350-750 kcmil
GENDER	Male
MATERIAL	Rubber
RECEPTACLE THREADED STUD SIZE	1/2"-13
SHAPE	90° angle
COLOR	Green

EB 94 - Cam-Lok E1017, E1019 and E1023 Connectors	
Eaton Specification Sheet - E1017-1608	
Cam-Lok Single Pole Plugs and Receptacles catalog	
Cam-Lok J Series Single Pole Plugs and Receptacles catalog page	

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: