

Eaton EABX16 ATEX

Eaton Crouse-Hinds series Condulet EAB ATEX conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, X shape, 1/2"

PRODUCT NAME	Eaton Crouse-Hinds series Condulet EAB ATEX conduit outlet box with cover
CATALOG NUMBER	EABX16 ATEX
UPC	662276049284
PRODUCT LENGTH/DEPTH	5.31 in
PRODUCT HEIGHT	5.31 in
PRODUCT WIDTH	2.53 in
PRODUCT WEIGHT	4.3 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	4
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

SHAPE	X
TRADE SIZE	1/2"
COVER OPENING DIAMETER	3"
MATERIAL	Feraloy iron alloy

[IF 1472 - EAB Condulet Conduit Outlet Bodies](#)

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

[Eaton Specification Sheet - EABX16 ATEX](#)

[Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page](#)

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification \(EAB\)](#)

[Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification \(EAB\)](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

