



□□□□

Eaton EATS16N-KR

16A EATON ATS 1P C19,C13/C19 KR 230V
COM

□□□□

PRODUCT NAME	Eaton ATS PDU
CATALOG NUMBER	EATS16N-KR
PRODUCT LENGTH/DEPTH	430 mm
PRODUCT HEIGHT	43 mm
PRODUCT WIDTH	250 mm
PRODUCT WEIGHT	3.54 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CE IEC 60950-1



Powering Business Worldwide

SPECIAL FEATURES

- Provides power redundancy to IT equipment
- Alternative to expensive redundant power supplies available from networking equipment vendors
- Compact, 1U rack form factor
- Seamlessly switches from one power source to the other
- Network management
- LCD with metering and basic configuration capabilities

TYPE	ATS
FORM FACTOR	1U
OUTLET CONTROL	No

PACKAGE CONTENTS

- ATS
- Quick start guide
- Safety manual
- 2 x Input cables: C19-C20 (1.80m)
- 2 x Input cable lockers
- Plastic strips for output locking
- RS232 cable
- DB9/RJ45 cable for network card configuration
- Accessories for rack installation

OPERATING TEMPERATURE	0° to 40°C (32° to 104°F)
MOUNTING DIRECTION	Horizontal
COLOR	Black
INPUT CONNECTION	(2) C20
CORD LENGTH	2m
WATTAGE	3.84 kW max
AMPERAGE RATING	16A
INPUT VOLTAGE	200-240V
PHASE	Single-phase

FREQUENCY RATING	50/60 Hz
OUTLETS	8XC13:1XC19
NUMBER OF OUTPUTS C13	8
NUMBER OF OUTPUTS C19	1
NUMBER OF OUTPUTS C20	2
NUMBER OF OUTPUTS HARDWIRED	0
NUM OF OUTPUTS PC (SCHUKO)	0
NUMBER OF OUTPUTS (OTHER)	0
NUMBER OF OUTLETS WITH EARTH PIN	9
SNMP	Yes
ETHERNET INTERFACE	Yes
SERIAL INTERFACE	No
MASS CONFIGURATION	Yes
ELECTRICAL CONNECTION	Connecting cord with plug
EVALUATION	At distance
MOUNTING DIMENSION (METRICAL)	43
MOUNTING DIMENSION (STANDARDIZED)	482.6 mm (19 inch)
SWITCHABLE	No
OVER VOLTAGE CATEGORY	2
FITTED WITH:	Display LED indication Ampere Meter Mounting material
COMMUNICATION	HTTP, HTTPS, SSL, Telnet, FTP, SNMP, SMTP, DNS, DHCP, LDAP, RADIUS

