

Eaton ED2N41171012

Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture, 3/4", Myers conduit hubs, zinc, one entry at each end, 50/60 Hz, 4 ft lamp, Polycarbonate lens, T8 bi-pin, Fiberglass-reinforced polyester, 1-lamp, Ceiling, 120-277 Vac, 32W

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture
CATALOG NUMBER	ED2N41171012
UPC	662276658721
PRODUCT LENGTH/DEPTH	53 in
PRODUCT HEIGHT	5.6 in
PRODUCT WIDTH	8.5 in
PRODUCT WEIGHT	17 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	Fluorescent
LAMP LENGTH	4 ft
LIGHT TYPE	T8 bi-pin
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MOUNTING	Ceiling
ENTRY SIZE	3/4"
ENTRY TYPE	Myers conduit hubs, zinc, one entry at each end
WATTAGE	32W
NUMBER OF LAMPS	1-lamp
MATERIAL	Fiberglass-reinforced polyester
LENS MATERIAL	Polycarbonate

3D

[Eaton Crouse-Hinds
ED2N41171012 3D
drawing](#)

[IF LBL1584 - Pauluhn ECOS
ED2N Series Linear
Fluorescent](#)

[Eaton Specification Sheet -
ED2N41171012](#)

[Crouse-Hinds series
Pauluhn ECOS Linear
Fluorescent brochure](#)

[Crouse-Hinds series
Pauluhn ECOS Linear
Fluorescent catalog page](#)

[Pauluhn ECOS Hazardous,
Harsh and Marine Linear
Fluorescent Light Fixtures
Canadian certification](#)

[Pauluhn ECOS Hazardous,
Harsh and Marine Linear
Fluorescent Light Fixtures
UL certification](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

