

## Eaton ED2N42171012

Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture,3/4" Myers conduit hubs,zinc,one entry at each end,4 ft,Polycarbonate lens,T8 bi-pin,Fiberglass-reinforced polyester,Ceiling mount,2-lamp,120-277 Vac,32W

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture
<b>CATALOG NUMBER</b>	ED2N42171012
<b>UPC</b>	662276420342
<b>PRODUCT LENGTH/DEPTH</b>	53 in
<b>PRODUCT HEIGHT</b>	5.6 in
<b>PRODUCT WIDTH</b>	8.5 in
<b>PRODUCT WEIGHT</b>	17 lb

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Hazardous/Classified Locations
<b>STANDARDS TYPE</b>	NEC/CEC
<b>NEC HAZARDOUS RATING</b>	Class I, Division 2 Class II, Division 1 Class III
<b>NEMA RATING</b>	4X
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

## Product specifications

<b>LAMP TYPE</b>	Fluorescent
<b>LAMP LENGTH</b>	4 ft
<b>LIGHT TYPE</b>	T8 bi-pin
<b>VOLTAGE RATING</b>	120-277 Vac
<b>FREQUENCY RATING</b>	50/60 Hz
<b>MOUNTING</b>	Ceiling
<b>ENTRY SIZE</b>	3/4"
<b>ENTRY TYPE</b>	Myers conduit hubs, zinc, one entry at each end
<b>WATTAGE</b>	32W
<b>NUMBER OF LAMPS</b>	2-lamp
<b>MATERIAL</b>	Fiberglass-reinforced polyester
<b>LENS MATERIAL</b>	Polycarbonate

### 3D

[Eaton Crouse-Hinds ED2N42171012 3D drawing](#)

[IF LBL1584 - Pauluhn ECOS ED2N Series Linear Fluorescent](#)

[Eaton Specification Sheet - ED2N42171012](#)

[Crouse-Hinds series Pauluhn ECOS Linear Fluorescent brochure](#)

[Crouse-Hinds series Pauluhn ECOS Linear Fluorescent catalog page](#)

[Pauluhn ECOS Hazardous, Harsh and Marine Linear Fluorescent Light Fixtures Canadian certification](#)

[Pauluhn ECOS Hazardous, Harsh and Marine Linear Fluorescent Light Fixtures UL certification](#)

---

:
:
:
:

---

Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com



© 2026