

Eaton

ED2N43171012EM1

Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent,3/4",Myers hubs,zinc,one entry at each end,4 ft,Polycarbonate lens,T8 bi-pin,Fiberglass-reinforced polyester,3-lamp,Emergency battery back-up,one lamp,Ceiling,120-277 Vac,32W

PRODUCT NAME	Eaton Crouse-Hinds series Pauluhn ECOS ED2N linear fluorescent light fixture
CATALOG NUMBER	ED2N43171012EM1
UPC	662276628144
PRODUCT LENGTH/DEPTH	53 in
PRODUCT HEIGHT	5.6 in
PRODUCT WIDTH	8.5 in
PRODUCT WEIGHT	18 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LAMP TYPE	Fluorescent
LAMP LENGTH	4 ft
LIGHT TYPE	T8 bi-pin
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MOUNTING	Ceiling
ENTRY SIZE	3/4"
ENTRY TYPE	Myers conduit hubs, zinc, one entry at each end
WATTAGE	32W
NUMBER OF LAMPS	3-lamp
MATERIAL	Fiberglass-reinforced polyester
LENS MATERIAL	Polycarbonate
SPECIAL FEATURES	Emergency battery back-up ballast, one lamp

[IF LBL1584 - Pauluhn ECOS ED2N Series Linear Fluorescent](#)

[Eaton Specification Sheet - ED2N43171012EM1](#)

[Crouse-Hinds series Pauluhn ECOS Linear Fluorescent brochure](#)

[Crouse-Hinds series Pauluhn ECOS Linear Fluorescent catalog page](#)

[Pauluhn ECOS Hazardous, Harsh and Marine Linear Fluorescent Light Fixtures Canadian certification](#)

[Pauluhn ECOS Hazardous, Harsh and Marine Linear Fluorescent Light Fixtures UL certification](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

