



□□□□□

Eaton EDS1155

Eaton Crouse-Hinds series EDS pushbutton control station, With pushbuttons, Feraloy iron alloy, Two circuit, 2, Single-gang, 2, Dead end, 1/2"

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series EDS pushbutton control station
CATALOG NUMBER	EDS1155
UPC	782274763651
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	5.91 in
PRODUCT WIDTH	5.81 in
PRODUCT WEIGHT	8.8 lb



Powering Business Worldwide

□□□□

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 7 9
ENCLOSURE TYPE	With pushbuttons
MATERIAL	Feraloy iron alloy
NORMAL POSITION	Two circuit
NUMBER OF DEVICES	2
NUMBER OF GANGS	Single-gang
NUMBER OF PUSHBUTTONS	2
STYLE	Dead end
TRADE SIZE	1/2"
VOLTAGE RATING	600 Vac

□□□□:

□□□□:

□□□:

□□:

00

3D	SP3D Design Package - EDS and EFS Explosionproof Control Stations
	IF 328 - EDS, EFS, EDSC and EFSC Single- and Two-gang Device Bodies
	IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations
	IF 372 - EDS Notice
	Eaton Specification Sheet - EDS1155
	EDS/EDSX Hazardous Area Control Stations catalog page
	EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations Canadian certification
	EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations UL certification