

Eaton EDS31101 W39

Eaton Crouse-Hinds series EDS manual motor starter control station, Single-pole, With switch, 1 HP, With one 1" hub, Feraloy iron alloy, Single-gang, With 16.00A Cutler Hammer heater, Dead end, 1"

PRODUCT NAME	Eaton Crouse-Hinds series EDS manual motor starter control station
CATALOG NUMBER	EDS31101 W39
UPC	662276488618
PRODUCT LENGTH/DEPTH	3.5 in
PRODUCT HEIGHT	6.03 in
PRODUCT WIDTH	5.06 in
PRODUCT WEIGHT	8.02 lb

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class II, Division 1 Class II, Division 2 Class III Class I, Division 2 Class I, Division 1
NEMA RATING	3 9 7
CONFIGURATION	Single-pole
ENCLOSURE TYPE	With switch
HORSEPOWER	1 hp
HUB STYLE	With one 1" hub
MATERIAL	Feraloy iron alloy
NUMBER OF GANGS	Single-gang
STYLE	Dead end
TRADE SIZE	1"
SPECIAL FEATURES	With 16.00A Cutler Hammer heater

	IF 372 - EDS Notice
	IF 242 - EDS and EDSC Control Stations
	IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations
	Eaton Specification Sheet - EDS31101 W39
	EDS Series Explosionproof Motor Starter Control Stations catalog page
	EDS Explosionproof Motor Starter Control Stations UL certification
	EDS Explosionproof Motor Starter Control Stations Canadian certification

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.