



□□□□□

Eaton EFLX12I

Eaton FlexPDU, 1U, C20 input, 4 kW, 16A, 200-240V, Outlets: (12) C13/(1) C19

□□□□

PRODUCT NAME	Eaton Flex Rack PDU
CATALOG NUMBER	EFLX12I
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	44 mm
PRODUCT WIDTH	483 mm
PRODUCT WEIGHT	1.6 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CE

SPECIAL FEATURES

- Extend the number of devices that can be connected to a single UPS
- Can be rackmounted, wallmounted or connected at the rear of a Eaton UPS in 3 different ways
- 1U versatile power distribution unit
- Easy plug-in connectivity
- Universal solution

TYPE	Rack PDU
FORM FACTOR	1U
OUTLET CONTROL	No

PACKAGE CONTENTS

- Rack PDU
- Mounting accessories
- Quickstart guide
- Safety Instructions

OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)
MOUNTING DIRECTION	Horizontal
COLOR	Black
INPUT CONNECTION	C20
CORD LENGTH	2m
WATTAGE	3.84 kW max
AMPERAGE RATING	16A
INPUT VOLTAGE	200-240V
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
NUMBER OF OUTPUTS C13	12
NUMBER OF OUTPUTS C19	1
NUMBER OF OUTLETS WITH EARTH PIN	13
SNMP	No
ETHERNET INTERFACE	No
SERIAL INTERFACE	No
MASS CONFIGURATION	No
ELECTRICAL CONNECTION	Socket outlet

EVALUATION	Other
MOUNTING DIMENSION (METRICAL)	44
MOUNTING DIMENSION (STANDARDIZED)	482.6 mm (19 inch)
SWITCHABLE	No
OVER VOLTAGE CATEGORY	2
AMPEREMETER	No
FITTED WITH:	Mounting material

□□□□:
□□□□:
□□□:
□□: