



□□□□□

Eaton EFLX6B

Eaton FlexPDU, 1U, C20 input, 4 kW, 16A, 200-240V, Outlets: (1) C19/(6) BS

□□□□

PRODUCT NAME	Eaton Flex Rack PDU
CATALOG NUMBER	EFLX6B
PRODUCT LENGTH/DEPTH	120 mm
PRODUCT HEIGHT	52 mm
PRODUCT WIDTH	483 mm
PRODUCT WEIGHT	1.6 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CE

SPECIAL FEATURES

- Extend the number of devices that can be connected to a single UPS
- Can be rackmounted, wallmounted or connected at the rear of a Eaton UPS in 3 different ways
- 1U versatile power distribution unit
- Easy plug-in connectivity
- Universal solution

TYPE	Rack PDU
FORM FACTOR	1U
OUTLET CONTROL	No

PACKAGE CONTENTS

- Rack PDU
- Mounting accessories
- Quickstart guide
- Safety Instructions

OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)
MOUNTING DIRECTION	Horizontal
COLOR	Black
INPUT CONNECTION	C20
CORD LENGTH	2m
WATTAGE	3.84 kW max
AMPERAGE RATING	16A
INPUT VOLTAGE	200-240V
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
NUMBER OF OUTPUTS C19	1
NUM OF OUTPUTS PC (SCHUKO)	6
NUMBER OF OUTPUTS (OTHER)	6
SNMP	No
ETHERNET INTERFACE	No
SERIAL INTERFACE	No
MASS CONFIGURATION	No
ELECTRICAL CONNECTION	Socket outlet

