

Eaton EFS200

Eaton Bussmann series low voltage british standard fuse, 200A, AC 415 V, V88/B2, 31 x 158 mm, gL/gG

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	EFS200
UPC	051712844888
PRODUCT LENGTH/DEPTH	209 mm
PRODUCT HEIGHT	39 mm
PRODUCT WIDTH	39 mm
PRODUCT WEIGHT	183 g
COMPLIANCES	RoHS Compliant

AMPERAGE RATING	200 A
FITTED WITH:	Centre bolted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	133 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
CLASS	Class gG/gL
FUSE TYPE	EFS
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	14 W
CONNECTION	133 mm fixing centre
CONSTRUCTION	BS88/B2
CONSTRUCTION SIZE	B2
FUSE SHAPE	Center bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	general industrial applications
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250944en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

