



□□□□□

Eaton EGB3025FFG

Eaton Series G molded case circuit breaker, EG-frame, EG, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 25A, 600Y/347 Vac, 25 kAIC at 240 Vac, 18 kAIC at 480 Vac, Line and load, 50/60 Hz

□□□□

PRODUCT NAME	Eaton Series G complete molded case circuit breaker
CATALOG NUMBER	EGB3025FFG
UPC	782116131310
PRODUCT LENGTH/DEPTH	2.99 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	3 in
PRODUCT WEIGHT	2.5 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed IEC Rated CSA Certified

□□□□	
AMPERAGE RATING	25 A
VOLTAGE RATING	600Y/347 Vac
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	EG
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series G
TERMINALS	Line and load
FRAME	EG
FREQUENCY RATING	50/60 Hz
INTERRUPT RATING	25 kAIC at 240 Vac 18 kAIC at 480 Vac
NUMBER OF POLES	Three-pole
TYPE	Complete breaker

□□	
□□□□	Comprehensive circuit protection for control panel applications
	Breaker service centers

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

