



□□□□□

Eaton EJB161608

Eaton Crouse-Hinds series EJB junction box, 16" x 16" x 8", Without hinge, Copper-free aluminum, Style C

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series EJB junction box
CATALOG NUMBER	EJB161608
UPC	782274017709
PRODUCT LENGTH/DEPTH	21.19 in
PRODUCT HEIGHT	21.19 in
PRODUCT WIDTH	10.88 in
PRODUCT WEIGHT	113 lb



Powering Business Worldwide

Eaton	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III Class I, Zone 1 Class I, Zone 2
NEMA RATING	3 3R 4 7 9
INGRESS PROTECTION (IP) RATINGS	IP66
ENCLOSURE SIZE	16" x 16" x 8"
HINGE	Without hinge
MATERIAL	Copper-free aluminum
STYLE	C

Links	
3D model	SP3D Design Package - EJB Explosionproof Enclosures
Product code	IF 931 - EJB, Style C Model M82 Series Junction Boxes
Specification sheet	Eaton Specification Sheet - EJB161608
	EJB Style C Enclosures
Product page	Crouse-Hinds series EJB Explosionproof Enclosures catalog page
	EJB Explosionproof Enclosures UL certification
	EJB Explosionproof Enclosures Canadian certification
