



□□□□

Eaton EMDH206

Eaton Moeller series xPole UK - EM.H MCB.
EM, 2-pole, trip type: D, rated current In: 6 A,
rated switching capacity IEC/EN 60947-2: 15
kA, rated switching capacity IEC/EN 60898-1:
10 kA

□□□□

PRODUCT NAME	Eaton Moeller series xPole UK - EM.H MCB
CATALOG NUMBER	EMDH206
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	73 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	0.24 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

□□□□

USED WITH	EM Miniature circuit breaker
AMPERAGE RATING	6 A
FEATURES	Additional equipment possible
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
TRIPPING CHARACTERISTIC	D
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
WIDTH IN NUMBER OF MODULAR SPACINGS	2
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Two-pole
RELEASE CHARACTERISTIC	D

□□

□□□□

[IL019071ZU](#)

