



Eaton EP-501060

HLN-C13/1N . Miniature circuit breaker (MCB), 13 A, 1p+N, characteristic: C



PRODUCT NAME	Eaton Moeller series xEffect - FAZ-DC MCB
CATALOG NUMBER	EP-501060
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	17.5 mm
PRODUCT WEIGHT	0.113 kg
COMPLIANCES	CE Marked RoHS conform



Powering Business Worldwide

□□□□

AMPERAGE RATING	13 A
VOLTAGE RATING	230 V AC
FREQUENCY RATING	50/60 Hz
POLLUTION DEGREE	2
DEGREE OF PROTECTION	IP20
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	3.4 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
AMBIENT OPERATING TEMPERATURE - MAX	75 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
BUILT-IN DEPTH	70.5 mm
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CURRENT LIMITING CLASS	3
FREQUENCY RATING - MAX	60 Hz
FREQUENCY RATING - MIN	50 Hz
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
WIDTH IN NUMBER OF MODULAR SPACINGS	1
VOLTAGE TYPE	AC
OVERVOLTAGE CATEGORY	III
NUMBER OF POLES	Single-pole + N

□□

CHARACTERISTIC CURVE	eaton-xeffect-faz-dc-mcb-characteristic-curve-005.jpg eaton-xeffect-faz-dc-mcb-characteristic-curve-003.jpg
PEP ECO-PASSPORT	eaton-non-selective-universal-mcb-pep-eato-00058-v0101-en.pdf
□□□□□	eaton-rccb-rcbo-g9-il019140zu.pdf
□□□	eaton-xeffect-faz-dc-mcb-wiring-diagram-003.jpg
□□	eaton-xeffect-faz-dc-mcb-dimensions-005.jpg eaton-xeffect-faz-dc-mcb-3d-drawing-002.jpg

