

Eaton EP-501335

EMC2-H212/55-W . Floor-standing
distribution board EMC2 empty, IP55,
protection class II,
HxWxD=1850x550x270mm, white (RAL
9016)

PRODUCT NAME	Eaton xEnergy Basic EMC2 enclosure floor-standing
CATALOG NUMBER	EP-501335
PRODUCT LENGTH/DEPTH	270 mm
PRODUCT HEIGHT	1850 mm
PRODUCT WIDTH	550 mm
PRODUCT WEIGHT	44 kg
CERTIFICATIONS	CE



FEATURES	EMC-version Connectable
FITTED WITH:	Door
SURFACE FINISHING	Powder coating
DEGREE OF PROTECTION	IP55 IK10 Other
MATERIAL QUALITY	Other
COLOR	White
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	960 N
NUMBER OF LOCKS	0
RAL-NUMBER	9016
MATERIAL	Steel
MOUNTING METHOD	Wall mounting
INSTALLATION TYPE	Floor standing wall model
NUMBER OF COVERS/DOORS	1
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	2000 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	100 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	118 W
NUMBER OF CONNECTOR HOLES	0



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

