



## Eaton ESD25

Eaton Bussmann series low voltage british standard fuse, 25A, AC 550 V, V88/F2, 14 x 68 mm, gL/gG

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series low voltage british standard fuse
<b>CATALOG NUMBER</b>	ESD25
<b>UPC</b>	051712844574
<b>PRODUCT LENGTH/DEPTH</b>	67 mm
<b>PRODUCT HEIGHT</b>	14 mm
<b>PRODUCT WIDTH</b>	14 mm
<b>PRODUCT WEIGHT</b>	30.5 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC 60269-2 BS88

□□□□

<b>AMPERAGE RATING</b>	25 A
<b>FITTED WITH:</b>	Offset bladed tags
<b>FUSE SIZE</b>	BS88/F2
<b>CURRENT TYPE</b>	AC
<b>BREAKING CAPACITY</b>	80 kA
<b>RATED SWITCHING CAPACITY</b>	80 kA
<b>RATED VOLTAGE AC</b>	550 V
<b>CLASS</b>	Class gG/gL
<b>FUSE TYPE</b>	ESD
<b>UTILIZATION CATEGORY</b>	gL/gG (cable protection/equipment protection)
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	80 kAIC
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>WATT LOSSES</b>	2 W
<b>CONNECTION</b>	Blade end
<b>CONSTRUCTION</b>	BS88/F2
<b>CONSTRUCTION SIZE</b>	F2
<b>FUSE SHAPE</b>	Offset bladed tags
<b>VOLTAGE TYPE</b>	AC
<b>SUITABLE FOR</b>	63ENS Safeloc fuse holder SC63 Safeclip fuse holder
<b>VOLTAGE RATING</b>	550 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	general industrial applications
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Fuse system E

□□

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250973en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025   

Follow us on social media to get the latest product and support information.

