

Eaton ESD32

Eaton Bussmann series low voltage british standard fuse, 32A, AC 550 V, V88/F2, 14 x 68 mm, gL/gG

| | |
|----------------------|---|
| | |
| PRODUCT NAME | Eaton Bussmann series low voltage british standard fuse |
| CATALOG NUMBER | ESD32 |
| UPC | 051712844581 |
| PRODUCT LENGTH/DEPTH | 67 mm |
| PRODUCT HEIGHT | 14 mm |
| PRODUCT WIDTH | 14 mm |
| PRODUCT WEIGHT | 30.5 g |
| COMPLIANCES | Contact Manufacturer |

| | |
|---|--|
| AMPERAGE RATING | 32 A |
| FITTED WITH: | Offset bladed tags |
| FUSE SIZE | BS88/F2 |
| CURRENT TYPE | AC |
| BREAKING CAPACITY | 80 kA |
| RATED SWITCHING CAPACITY | 80 kA |
| RATED VOLTAGE AC | 550 V |
| CLASS | Class gG/gL |
| FUSE TYPE | ESD |
| UTILIZATION CATEGORY | gL/gG (cable protection/equipment protection) |
| COLOR | None |
| INTERRUPT RATING | 80 kAIC |
| FUSE INDICATOR | None |
| INSULATED METAL GRIPPING LUGS (IMGL) | No |
| WATT LOSSES | 2.9 W |
| CONNECTION | Blade end |
| CONSTRUCTION | BS88/F2 |
| CONSTRUCTION SIZE | F2 |
| FUSE SHAPE | Offset bladed tags |
| VOLTAGE TYPE | AC |
| SUITABLE FOR | 63ENS Safeloc fuse holder SC63 Safeclip fuse holder |
| VOLTAGE RATING | 550 V |
| TYPE | Fuse |
| APPLICATION | general industrial applications |
| FUSE SYSTEM (ACCORDING TO IEC 60269) | Fuse system E |

DECLARATIONS OF CONFORMITY

[eaton-low-voltage-british-standard-fuse-declaration-of-conformity-uk250973en.pdf](#)

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

