



□□□□□

Eaton EVLEDBX3C201

Eaton Crouse-Hinds series EV LED light fixture, 0.06 - 0.17A, Cool white, AC drive, Heat and impact resistant glass globe, With guard, 1500 lumens, 100 lm/W, Copper-free aluminum, Wall mount, >0.90 power factor, 1", 100-277 Vac, 15W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series EV LED light fixture
CATALOG NUMBER	EVLEDBX3C201
UPC	662276281455
PRODUCT LENGTH/DEPTH	12.56 in
PRODUCT HEIGHT	16.81 in
PRODUCT WIDTH	7.25 in
PRODUCT WEIGHT	11.1 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Zone 1 Class I, Zone 2 Class II, Division 1
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Wall
TRADE SIZE	1"
GUARD	With guard
DRIVE TYPE	AC
VOLTAGE RATING	100-277 Vac
FREQUENCY RATING	50/60 Hz
WATTAGE	15W
AMPERAGE RATING	0.06 - 0.17A
POWER FACTOR	>0.90
MATERIAL	Copper-free aluminum
GLOBE MATERIAL	Heat and impact resistant glass
EQUIVALENT LUMINAIRE	100-200W incandescent




3D CAD DRAWING PACKAGE

[Eaton Crouse-Hinds EVLEDBX3C201 3D drawing](#)



[IF 1562 - Hazard-Gard EV LED](#)



[Eaton Specification Sheet - EVLEDBX3C201](#)



[Crouse-Hinds series Global LED lighting portfolio](#)



[Crouse-Hinds series Hazard-Gard EV LED catalog page](#)



[EV LED Explosionproof LED Light Fixtures UL certification \(Marine\)](#)

[EV LED Explosionproof LED Light Fixtures UL certification](#)

[EV LED Explosionproof LED Light Fixtures Canadian certification](#)

