



□□□□□

Eaton EVLLA11LCM1-UNV1

Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture, Cool white, 250W-320W HID equiv, Stainless steel guard, Shatter-resistant glass lens, 11000 lumens, 104 lm/W, Copper-free aluminum, Mounting module adapter, 120-277 Vac, 115W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture
CATALOG NUMBER	EVLLA11LCM1-UNV1
UPC	662276993822
PRODUCT LENGTH/DEPTH	15.9 in
PRODUCT HEIGHT	11.97 in
PRODUCT WIDTH	15.9 in
PRODUCT WEIGHT	55 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	104
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Mounting module adapter
EQUIVALENT LUMINAIRE	250W-320W HID
GUARD TYPE	Stainless steel
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MATERIAL	Copper-free aluminum
LENS MATERIAL	Shatter-resistant glass
WATTAGE	115W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90

□□

[IF 1913 - EVLLA Hazard-Gard LED Luminaire](#)

□□□□□

[IF 1914 - EVLLA Hazard-Gard LED Luminaire Driver Replacement](#)

□□□□□□□

[Eaton Specification Sheet - EVLLA11LCM1-UNV1](#)

[Hazard-Gard EVLL LED Explosionproof](#)

[Crouse-Hinds series DLC approved lighting products](#)

□□□□

[Crouse-Hinds series Hazard-Gard EVLL LED brochure](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

□□□□

[Crouse-Hinds series Hazard-Gard EVLLA LED catalog page](#)

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures UL certification](#)

□□□□

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures Canadian certification](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

