



□□□□

Eaton EVLLA11LW0-UNV1

Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture, Warm white, 250W-320W HID equivalent, No guard, Shatter-resistant glass lens, 11000 lumens, 104 lm/W, Copper-free aluminum, No mounting module, 120-277 Vac, 115W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture
CATALOG NUMBER	EVLLA11LW0-UNV1
UPC	662276993235
PRODUCT LENGTH/DEPTH	15.9 in
PRODUCT HEIGHT	11.97 in
PRODUCT WIDTH	15.9 in
PRODUCT WEIGHT	53 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	104
COLOR TEMPERATURE	Warm white
MOUNTING METHOD	No mounting module
EQUIVALENT LUMINAIRE	250W-320W HID
GUARD TYPE	No guard
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MATERIAL	Copper-free aluminum
LENS MATERIAL	Shatter-resistant glass
WATTAGE	115W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90

□□

[IF 1913 - EVLLA Hazard-Gard LED Luminaire](#)

□□□□□

[IF 1914 - EVLLA Hazard-Gard LED Luminaire Driver Replacement](#)

□□□□□□□

[Hazard-Gard EVLL LED Explosionproof](#)

[Eaton Specification Sheet - EVLLA11LW0-UNV1](#)

[Crouse-Hinds series Hazard-Gard EVLL LED brochure](#)

□□□□

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

□□□□

[Crouse-Hinds series Hazard-Gard EVLLA LED catalog page](#)

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures UL certification](#)

□□□□

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures Canadian certification](#)

