

# Eaton EVLLA11LWA20-UNV34-S812

Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture, Warm white, 250W-320W HID equiv, No guard, Shatter-resistant glass lens, 11000 lumens, 104 lm/W, Copper-free aluminum, Pendant mount, Trunnion mount kit, 3/4", 347-480 Vac, 115W

|                             |                                                               |
|-----------------------------|---------------------------------------------------------------|
|                             |                                                               |
| <b>PRODUCT NAME</b>         | Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture |
| <b>CATALOG NUMBER</b>       | EVLLA11LWA20-UNV34-S812                                       |
| <b>UPC</b>                  | 662276994317                                                  |
| <b>PRODUCT LENGTH/DEPTH</b> | 16.32 in                                                      |
| <b>PRODUCT HEIGHT</b>       | 15.42 in                                                      |
| <b>PRODUCT WIDTH</b>        | 16.32 in                                                      |
| <b>PRODUCT WEIGHT</b>       | 55 lb                                                         |

## Certifications and compliances

|                                 |                                                          |
|---------------------------------|----------------------------------------------------------|
| AREA CLASSIFICATION             | Hazardous/Classified Locations                           |
| STANDARDS TYPE                  | NEC/CEC                                                  |
| NEC HAZARDOUS RATING            | Class I, Division 1<br>Class II, Division 1<br>Class III |
| NEMA RATING                     | 4X                                                       |
| INGRESS PROTECTION (IP) RATINGS | IP66                                                     |

## Product specifications

|                      |                          |
|----------------------|--------------------------|
| LUMENS               | 11000                    |
| LUMENS PER WATT      | 104                      |
| COLOR TEMPERATURE    | Warm white               |
| MOUNTING METHOD      | Pendant                  |
| EQUIVALENT LUMINAIRE | 250W-320W HID            |
| TRADE SIZE           | 100-240 Vac, 127-250 Vdc |
| GUARD TYPE           | No guard                 |
| VOLTAGE RATING       | 347-480 Vac              |
| FREQUENCY RATING     | 50/60 Hz                 |
| MATERIAL             | Copper-free aluminum     |
| LENS MATERIAL        | Shatter-resistant glass  |
| WATTAGE              | 115W                     |
| DIMMING              | Dimmable driver          |
| POWER FACTOR         | > 0.90                   |

[IF 1913 - EVLLA Hazard-Gard LED Luminaire](#)

[IF 1914 - EVLLA Hazard-Gard LED Luminaire Driver Replacement](#)

[Hazard-Gard EVLL LED Explosionproof](#)

[Eaton Specification Sheet - EVLLA11LWA20-UNV34-S812](#)

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Hazard-Gard EVLL LED brochure](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Hazard-Gard EVLLA LED catalog page](#)

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures UL certification](#)

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures Canadian certification](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

