



□□□□

Eaton EVLLA13LCBX30-UNV1

Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture, Cool white, 320W-400W HID equivalent, No guard, Shatter-resistant glass lens, 13000 lumens, 100 lm/W, Copper-free aluminum, Wall mount, 1", 120-277 Vac, 130W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Hazard-Gard EVLLA LED light fixture
CATALOG NUMBER	EVLLA13LCBX30-UNV1
UPC	662276991286
PRODUCT LENGTH/DEPTH	17.54 in
PRODUCT HEIGHT	14.9 in
PRODUCT WIDTH	16.05 in
PRODUCT WEIGHT	56 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	13000
LUMENS PER WATT	100
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Wall
EQUIVALENT LUMINAIRE	320W-400W HID
TRADE SIZE	1"
GUARD TYPE	No guard
VOLTAGE RATING	120-277 Vac
FREQUENCY RATING	50/60 Hz
MATERIAL	Copper-free aluminum
LENS MATERIAL	Shatter-resistant glass
WATTAGE	130W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90

□□

□□□□□

[IF 1914 - EVLLA Hazard-Gard LED Luminaire Driver Replacement](#)

[IF 1913 - EVLLA Hazard-Gard LED Luminaire](#)

□□□□□□□

[Eaton Specification Sheet - EVLLA13LCBX30-UNV1](#)

[Hazard-Gard EVLL LED Explosionproof](#)

[Crouse-Hinds series Hazard-Gard EVLL LED brochure](#)

□□□□

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

□□□□

[Crouse-Hinds series Hazard-Gard EVLLA LED catalog page](#)

□□□□

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures Canadian certification](#)

[Hazard-Gard EVLLA Explosionproof LED Light Fixtures UL certification](#)

