



Eaton EXP-W10

10 wired zone expander, 4 outputs, bus connected

□□□□

PRODUCT NAME	Eaton EXP intruder system expander
CATALOG NUMBER	EXP-W10
PRODUCT LENGTH/DEPTH	41 mm
PRODUCT HEIGHT	230 mm
PRODUCT WIDTH	144 mm
PRODUCT WEIGHT	0.46 kg
CERTIFICATIONS	CE marking



Powering Business Worldwide

TYPE	Expander
BATTERY CHARGE OUTPUTS	0
COLOUR	White
CURRENT - MAX	20 mA
CURRENT NORMAL	20 mA
DATA SHEETS	EXP-R10/30
DEDICATED PA KEYS	No
DEVICE CONNECTIONS	Wired
DISPLAY	No
EMERGENCY POWER SUPPLY INTEGRATED	No
EN 50131 GRADE	3
ENVIRONMENTAL CLASS	2
EXTERNAL PROX	No
INTEGRATED DIAL DEVICE	No
INTERFACE EXTERNAL	No
INTERNAL PROX	No
LOUDSPEAKER CONNECTION	Yes
NUMBER OF ASSAULT GROUPS	0
NUMBER OF INDICATOR GROUPS	0
NUMBER OF SABOTAGE GROUPS	11
NUMBER OF OUTPUTS FOR ACOUSTIC SIGNAL GENERATORS	0
NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS	0
OCCURRENCE MEMORY	No
OPERATING TEMPERATURE - MAX	55 °C
OPERATING TEMPERATURE - MIN	-10 °C
RADIO CONNECTION	No
RADIO FREQUENCY	Not applicable
RECHARGEABLE BATTERY	Not applicable
SUITABLE FOR BUS CONNECTION	Yes
SUPPLY - MAX	13.8 V
SUPPLY - MIN	10 V

