



Eaton F8570

Eaton Moeller series Plug in lighting range (LSC) - Wiring Devices. LSC ceiling assembly, 3pin, c/w 2m 0.75qmm HR (heat resistant) cable



PRODUCT NAME	Eaton Moeller series Plug in lighting range (LSC) - Wiring devices
CATALOG NUMBER	F8570
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	90 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.228 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	BS 6972 BS 7001 BS EN 5025-2-11



Powering Business Worldwide

□□□□

FEATURES	Halogen free
FITTED WITH:	Strain relief
POLLUTION DEGREE	2
INGRESS PROTECTION (IP) RATINGS	IP20
SPECIAL FEATURES	Terminal Screw Zinc Coated Steel with clear Passivation
TYPE	Litelink LSC
AMPERAGE RATING	6 A
VOLTAGE RATING	250 V AC
CONTACT MATERIAL	Other
ENCLOSURE MATERIAL	Other
HEAD STYLE	Combination head
NUMBER OF POLES	Three-pole
COLOR	White
CONNECTION TYPE	Screw connection
FIXING CENTERS	50.8 mm
FRONT PLATE COLOR/FINISHING	White
FRONT PLATE MATERIAL	Thermoplastic
BASE MATERIAL	Thermoplastic
SURFACE FINISHING OF CONTACTS	Other
TERMINAL MATERIAL	Brass
CONNECTABLE CONDUCTOR CROSS SECTION (FINE STRAND) - MAX	4 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (FINE STRAND) - MIN	4 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	2.5 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	2.5 mm ²
CONTINUITY RESISTOR	0 mΩ
CONTINUOUS TEMPERATURE RESISTANCE (CONTACT PART) - MAX	0 °C
CONTINUOUS	0 °C

□□

□□□□	eaton-brochure-xcomfort-bridge-br005016en-en-us.pdf
□□□□	eaton-power-defense-molded-case-circuit-breakers-catalog-ca013004en-en-us.pdf

