

Eaton FER1D2214SN

Female plug for 19 #16 contacts, insulator orientation N; FER1D2214SN

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	FER1D2214SN
PRODUCT LENGTH/DEPTH	44 mm
PRODUCT HEIGHT	44 mm
PRODUCT WIDTH	45.6 mm
PRODUCT WEIGHT	67 g

ENVIRONMENTAL CONDITIONS	RoHS
	Flammability rating UL94
	V0
	REACH
	Fire & Smoke

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
-------------------------------	--

CONNECTOR ORIENTATION	W
--------------------------	---

CONNECTOR TYPE	Plug
----------------	------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Socket (Female)
----------------	-----------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	Thread
---------------	--------

DEGREE OF PROTECTION	IP67
----------------------	------

LAYOUT	14
--------	----

PLUG TYPE	Straight Plug
-----------	---------------

SHELL CONTINUITY	20.0
------------------	------

SHELL MATERIAL	Aluminium
----------------	-----------

SHELL SIZE	22
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	100 °C
--------------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
--------------------------------	--------

NUMBER OF CONTACTS	19
--------------------	----

NUMBER OF CAVITY #16	19
----------------------	----

SALT SPRAY	500 hour
------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
