



Eaton FER1D2214SZ

Female plug for 19 #16 contacts, insulator orientation Z; FER1D2214SZ

□□□□

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
---------------------	---

CATALOG NUMBER	FER1D2214SZ
-----------------------	-------------

PRODUCT LENGTH/DEPTH	44 mm
-----------------------------	-------

PRODUCT HEIGHT	44 mm
-----------------------	-------

PRODUCT WIDTH	45.6 mm
----------------------	---------

PRODUCT WEIGHT	67 g
-----------------------	------



Powering Business Worldwide

ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 V0 REACH Fire & Smoke
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Thread
DEGREE OF PROTECTION	IP67
LAYOUT	14
PLUG TYPE	Straight Plug
SHELL CONTINUITY	20.0
SHELL MATERIAL	Aluminium
SHELL SIZE	22
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #16	19
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: