



## Eaton FH10

Eaton A200/B100 heater, Used with Starter Sizes 0,1, and 2, A200/B100 Heater, NEMA, Ambient .51-.55, .59 -.64A, Non-Comp .48-.51, .57 -.63A, Used with Starter Sizes 0,1, and 2, Type A and B, Thermal and Fast Trip



|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton A200/B100 heater   |
| <b>CATALOG NUMBER</b>       | FH10   |
| <b>UPC</b>                  | 786678629179   |
| <b>PRODUCT LENGTH/DEPTH</b> | 2.1 in   |
| <b>PRODUCT HEIGHT</b>       | 0.8 in   |
| <b>PRODUCT WIDTH</b>        | 1.3 in   |
| <b>PRODUCT WEIGHT</b>       | 0.03 lb  |
| <b>CERTIFICATIONS</b>       | UL Listed<br>CSA Certified   |
| <b>CATALOG NOTES</b>        | Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters |



Powering Business Worldwide

