



□□□□

Eaton FMVA-11-76-M20-UNV1-M2

Eaton Crouse-Hinds series Champ FMVA LED floodlight, 0.79 - 0.28A, Cool white, 20 mm entry, Heat and impact resistant glass lens, 11000 lumens, 158 lm/W, Die cast aluminum, Yoke mount, 7x6 optics, Gray epoxy powder coat, 100-277 Vac, 77W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ FMVA LED floodlight
CATALOG NUMBER	FMVA-11-76-M20-UNV1-M2
UPC	662277153041
PRODUCT LENGTH/DEPTH	16.12 in
PRODUCT HEIGHT	14.94 in
PRODUCT WIDTH	9.94 in
PRODUCT WEIGHT	24.92 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IECEX/ATEX IEC
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP67 IP66

Product specifications

LAMP TYPE	LED
LUMENS	11000
LUMENS PER WATT	158
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Yoke
VOLTAGE RATING	100-277 Vac
FREQUENCY RATING	50/60 Hz
OPTICAL DISTRIBUTION	7x6
ENTRY SIZE	20 mm
LENS MATERIAL	Heat and impact resistant glass
WATTAGE	77W
POWER FACTOR	> 0.90
AMPERAGE RATING	0.79 - 0.28A
MATERIAL	Die cast aluminum
SPECIAL FEATURES	Gray epoxy powder coat

□□

3D □□ [SP3D Design Package - Champ FMVA LED Hazardous Area Floodlights](#)

□□□□□ [IF 1956 - Champ FMVA M2 9L-15L LED Luminaire](#)

□□□□□□□ [Crouse-Hinds series FMVA LED Floodlights IES photometric files](#)

□□□□ [Crouse-Hinds series Champ FMVA LED Floodlights - 9,000 to 15,000 lumens brochure](#)

□□□□ [Crouse-Hinds series Champ FMVA LED Floodlights - 9,000 to 15,000 lumens catalog page](#)

