



□□□□□

## Eaton FP1308R2-R21-R

Eaton FP1308R inductor, 0.21 uH, 45 A Irms, 80 A ISAT, 0.58 mΩ resistance, SMT mounting, Ferrite, 2-pins, 400 qty.

□□□□

|                             |                        |
|-----------------------------|------------------------|
| <b>PRODUCT NAME</b>         | Eaton FP1308R inductor |
| <b>CATALOG NUMBER</b>       | FP1308R2-R21-R         |
| <b>UPC</b>                  | 051712234597           |
| <b>PRODUCT LENGTH/DEPTH</b> | 13.7 mm                |
| <b>PRODUCT HEIGHT</b>       | 8 mm                   |
| <b>PRODUCT WIDTH</b>        | 12.95 mm               |
| <b>PRODUCT WEIGHT</b>       | 5.89 g                 |
| <b>COMPLIANCES</b>          | RoHS Compliant         |

| FP1308R               |               |
|-----------------------|---------------|
| TYPE                  | Inductor      |
| MOUNTING              | SMT           |
| IRMS                  | 45 A          |
| ISAT                  | 80 A          |
| PACKAGE QUANTITY      | 400           |
| MATERIAL              | Ferrite       |
| FREQUENCY RATING      | Up to 2 MHz   |
| CONTACT CONFIGURATION | Two-pin       |
| TEMPERATURE RATING    | -40 to 125 °C |
| RESISTANCE            | 0.58 mΩ       |
| SERIES                | FP1308R       |

00

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| 00:             |



0000  
Eaton House  
30 Pembroke Road  
Dublin 4, 0000  
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

